

ABCOR® FEG™ PLUS MODULE: 10-HFP-276-PVI

Industrial Tubular Ultrafiltration One-Inch Modules

PRODUCT DESCRIPTION

KMS Part Number (KPN): 0711650 Membrane Chemistry: PVDF

Membrane Type: HFP (negatively charged)

Membrane Area: 2.2 ft² (0.20 m²)

Molecular Weight Cut-off: 120,000 Dalton (nominal)

Housing Construction: CPVC

Seal: CPVC Insert (Epoxied in Place)

Gasket: Viton®

Interconnecting Components: See Reverse

OPERATING AND DESIGN INFORMATION*

Maximum Inlet Pressure: 90 psi @ 140°F (6.2 bar @ 60°C)

Minimum Outlet Pressure: 5 psi (0.3 bar)
Maximum Operating Temperature (at pH 8.0): 140°F (60°C)
Maximum Permeate Side Back Pressure: 5 psi (0.6 bar)

Maximum Feed Side Pressure Drop: 10 psi @ 140° F (0.7 bar @ 60° C) Allowable pH - Continuous Exposure: 2.0 - 10.0 @ 140° F (60° C) Allowable pH - Short Term Exposure: 1.5 - 10.5 @ 140° F (60° C)


* Consult KMS Process Technology for specific applications.

FEED FLOW VS. PRESSURE DROP*

Circulation Flow		Crossflow Velocity		Pressure Drop	
gpm	m³/hr	fps	m/s	psi	bar
19	4.3	7.8	2.4	2.0	0.14
30	6.8	12.3	3.7	4.3	0.29
38	8.6	15.5	4.7	6.0	0.41


Koch Membrane Systems, Inc. must review operating and cleaning conditions for all new plants as well as changes to any existing plants. Data based on Water at 77° F and a specific gravity of 1.0. Circulation rates exhibit variances of 15%.

NOMINAL DIMENSIONS



ANCILLARY PARTS

KMS recommends that these membranes be used with KMS supplied ancillary parts. Sealing is provided by o-rings and gaskets. No additional sealing compound or tape is recommended for use on threaded connections.



KPN

0211786

0211803

0211804

0230091

Permeate Pass Kit (for 4 tubes)

O-Ring 2-112 (x4) Adapter $\frac{1}{4}$ to $\frac{3}{8}$ (x1)

Permeate Elbow Connector

Snap-Ring (x2)

Permeate Tee Connector (x4) Permeate Elbow Connector (x4)

CPVC interconnector (x1)

PVC Nut Holding (x2)

Includes:

PE tubing Permeate Tee Connector

10 Interconnector Kit. CPVC

Includes:

MEMBRANE INCOMPATIBILITY

Prior to exposing the membrane to any chemical, the chemical should be reviewed by Koch Membrane Systems. Aside from the listed chemicals below, synthetic coolants, semi-synthetic coolants, kerosenes, naphtha, gasoline, floc polymers may affect membrane performance.

Chemicals that should be avoided include the following:

- Aprotic Solvent (e.g., Dimethyl Formamide, Dimethyl Acetamide, N-Methyl Pyrolidine, etc.)
- Chlorinated Solvents (e.g., Methylene Chloride, Chloroform, Carbon Tetrachloride, etc.)
- Ketones (e.g., Acetone, Diacetone Alcohol, etc.)
- Silicones or Silicone based Defoamers (e.g., Siloxane)

The information contained in this publication is believed to be accurate and reliable, but is not to be construed as implying any warranty or guarantee of performance. We assume no responsibility, obligation or liability for results obtained or damages incurred through the application of the information contained herein. Refer to Standard Terms and Conditions of Sale and Performance Warranty documentation for additional information.

Koch Membrane Systems, Inc., www.kochmembrane.com

Corporate Headquarters: 850 Main Street, Wilmington, Massachusetts 01887-3388, USA, Tel. Toll Free: 1-888-677-5624, Telephone: 1-978-694-7000, Fax: 1-978-657-5208 European Headquarters: Koch Chemical Technology Group Ltd., The Granary, Telegraph Street, Stafford ST17 4AT, United Kingdom, Telephone: +44-178-527-2500, Fax: +44-178-522-3149

> • San Diego, California • Aachen, Germany • Lyon, France • Madrid, Spain • Milan, Italy • Wijnegem, Belgium • Beijing & Shanghai, China • Mumbai, India • · Melbourne, Australia · Singapore · Sao Paulo, Brazil · Manama, Kingdom of Bahrain ·